Entanglement | E21256-20BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A network of wire and crystal are suspended within a box frame illuminated from above. The light panel above highlights the iridescence of the crystal while providing ample illumination to the space below.



*max overall height

MEASUREMENTS

DIMENSION	: 47.25" L x 10" W x 6.75" H
MAX OAH	: 129" OAH
CANOPY	: 6" W x 1.75" H x 18" L
HANGING WEIGHT	: 18.7 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,550 Rated (1,900 Del.)
BULB	: 1 x 59W LED DC Integrated , 59W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 30-35-40K

FINISHES OPTION

Black (BK)

GLASS

Crystal 20

MATERIAL

Steel, Crystal

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com