

# MAGNETIC STIRRER

PCE-MSR 40



## Specification

### Speed

Measuring range up to 50 ... 1000 U/min

Resolution 1 U/min

Accuracy  $\pm 10$  U/min

### General technical data

Display Typ LCD

Display size 3,7 Inch

Dimensions Stirring plate: 392 x 396mm  
Stirring rod:  $\varnothing 10 \times 80$  mm

Performance 60 W

Number of stirring points 1

Drive of the stirring points Brushless motor

Max. Stirring quantity 50 L

Stirring plate material PC

Timer from 1 s

Timer until 100 h

Max. Stirring viscosity 10000 mPa.s

Menu language English (US), English (GB)

Protection class (device) IP20

Power supply 100 ... 240 V AC | 50/60 Hz

Connector type IEC plug

Operating conditions 0 ... 50 °C, 0 ... 80 %RH

Storage conditions 0 ... 50 °C, 0 ... 80 %RH

Dimensions ( L x W x H ) 490 x 400 x 85 mm

Weight 5419 g