

DAYA

H1098101-AGB

Like a drop of morning dew, the Daya sconce delights with an opalescent, slightly botanical influence. Each reflective glass orb is tinted in a champagne finish and inside etched for a serene, glowing effect. Finished in Aged Brass, the curved armature culminates in a delicately scalloped fitter reminiscent of a flower. Available with 1 or 2 lights.

FINISHES

AGED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 12.5"

Width/Diameter: 6"

Length: 7.5"

Canopy/Backplate: 4.75"

Product Weight: 2lb

Extension: 7.5"

Top to Center: 10.75"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Etched Champagne

Shade 1 Top Width: 6"

Shade 1 Height: 5.25"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 17" x 12" x 10"

Carton 1 Weight: 3lb

Shipping Method: Ground

Country of Origin: VN

