



TEGERA® 737

Learn more

FULLY DIPPED, SANDY FINISH ON PALM

Excellent multi-purpose glove for wet and oily environments. Fully nitrile dipped for durable protection. Sandy finish on palm for enhanced grip. Cut resistance level A. Very flexible and comfortable thanks to the ergonomic seamless design. Dark blue and black colours are dirt masking and suitable for extended product use.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Very durable
- Good grip
- Comfortable

FUNCTIONS

- Water and oil repellent
- Soft

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Contact with moisture, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Moist environments, Oily and greasy environments, Dirty environments

PRIMARY AREAS OF USE

Agricultural work, Building and construction, Carpentry, Concrete work, Construction, Engineering, Forest work, Gardening, HVAC installation, Machine operating, Mining, Painting, Paper industry work, Repair work, Sanitation, Soil preparation, Wood industry work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Transport equipment manufacturing, Agriculture, forestry and fishing, Oil and gas extraction, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Electricity and gas supply, Building and construction, Mining and quarrying, Pulp and paper

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE All-round work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 15
LINING MATERIAL Nylon
LENGTH 220-260 mm
DEXTERITY 5
GRIP DESIGN Sandy finish
COLOUR Black
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Bag with euro slot
DIPPING Fully dipped
DIPPING MATERIAL Nitrile
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level A
CUT RESISTANCE (EN ISO 13997) TDM: 3 N
INNER MATERIAL SPECIFICATION Nylon
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018
4141A

ANSI 6 ABR

FEATURES

Water repellent

SIZE		ARTICLE NUMBER	EAN
6	XS	737-6	7340118380926
7	S	737-7	7392626075061
8	M	737-8	7392626075078
9	L	737-9	7392626075085
10	XL	737-10	7392626075047
11	XXL	737-11	7392626075054

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.