SWIFTWALL®

TEMPORARY WALL SOLUTIONS

BUYER'S GUIDE

CREATE. DIVIDE. TRANSFORM.

PURCHASING GUIDE












Purchasing Guide	SWIFTWALL® PRO	SWIFTWALL® MAX	SWIFTWALL® FLEX	SWIFTWALL® CLICK	SWIFTWALL® LITE
Installation Speed	●●●	●●●	●●●	●●●●	●●●
Tool-Free Assembly	—	—	—	✓	—
Reconfigurable	✓	✓	✓	✓	✓
Durability	●●●	●●●●	●●	●●	●
Sound Control	✓	✓	✓	✓	✓
Graphic Ready	✓	✓	✓	✓	✓
Doors & Access	✓	✓	✓	✓	✓
Best For Primary Applications	Hospitality, Events, Construction Partition, Government, Retail, Residential	Airport Infastructure, Construction, Outdoor Construction, Customer Entry Tunnel	Healthcare, Airport Infastructure, Negative Air	Events, Popup Stores, Retail, Offices, Tactical Training, Residential	Residential, Dust Barrier
Single Panel Max Height	16ft	12ft	12.3ft	10ft	10ft
Is it Stackable?	✓	✓	—	—	✓
Single Panel Max Width	4ft	2ft	4ft	4ft	4ft
Fire Rating Options	Class A & Class C	Class A (non-combustable)	Class A & Class C	Class A & Class C	Class C
Can be Cut Onsite	✓	✓	Not Recommended	Not Recommended	✓
Available Finishes	ABS & Painted Aluminum	Powder Coated Aluminum	ABS & Painted Aluminum	ABS & Painted Aluminum	ABS

SWIFTWALL® PRO SWIFTWALL® MAX SWIFTWALL® FLEX SWIFTWALL® CLICK SWIFTWALL® LITE

SWIFTWALL®

SWIFTWALL PRO

Our SwiftWall Pro product line is an excellent choice for temporary modular wall construction with windows and doors for extended-use spaces.



SwiftWall Pro temporary wall systems consists of panels, channels and rails as well as optional components like doors and windows. Endless configuration options can be created for free-standing structures, wells, enclosures and displays.

- SwiftWall is the trusted product for use in construction, manufacturing , office, and event applications
- 5x faster install than stud & drywall - simple, fast, clean. 80% less labor costs
- Durable & lightweight - single person lift 35 lb. 8’ panel

PRO PANELS

Isolate and contain dust, separate and partition rooms, build entire events and more. Made of fire rated, non-hydroscopic swiftwall panels keep the noise down with an STC21 sound rating.

Standard panels are manufactured to a sturdy 4’ wide and 1” thick. All product lines come in heights of 8’ and 10‘ and most come in 12’, and 16’ also. Panels can be stacked as high as required by using C-channels and a support skeleton such as metal stud framing. Consult with a SwiftWall sales representative for more information.

Standard Sizes

4’
8’
10’
12’
16’
All standard sizes are manufactured to 4’ wide by 1” thick

Material

ABS with aluminum joiners and polyisocyanurate core (Class C Fire-Rated)
Matte painted aluminum skin with aluminum joiners and polyisocyanurate core (Class A Fire-Rated)


Finish

Option 1: White light-sheeen matte hair-cell ABS
Option 2: Standard coated semi-gloss aluminum (Class A Only)
Option 3: Powder coating upon request

SDS

Printed copies available upon request

Standard Panels



Acrylic Panels





SWIFTWALL PRO SWIFTWALL MAX SWIFTWALL FLEX SWIFTWALL CLICK SWIFTWALL LITE

SWIFTWALL

PRO PARTS



Click Panels (Class A & C)



Door Panel




Window Panels



Track



C-Channel




90-Degree Corner



Adjustable Corner

RECOMMENDED PARTS



Double Sided Tape

Provides additional stability during installation.



Extra Self-Drilling Screws

Secures the panels to the track, c-channel, and ceiling

SWIFTWALL PRO SWIFTWALL MAX SWIFTWALL FLEX SWIFTWALL CLICK SWIFTWALL LITE

SwiftWall Pro Class C Series

Product Type	Product #	Height (in)	Width (in)	Thickness (in)
Panel	P-P-ABS-08-48-W	95.5	48	1.12
	P-P-ABS-10-48-W	119.5		
	P-P-ABS-12-48-W	143.5		
	P-P-ABS-16-48-W	191.5		
Window Panel	P-P-ABS-08-48-W-W	95.5		
	P-P-ABS-10-48-W-W	119.5		
	P-P-ABS-12-48-W-W	143.5		
	P-P-ABS-16-48-W-W	191.5		
Single Door Panel	P-DS-ABS-08-48-W	95.5		
	P-DS-ABS-10-48-W	119.5		
	P-DS-ABS-12-48-W	143.5		
	P-DS-ABS-16-48-W	191.5		
Double Door Panel	P-DD-ABS-08-48-W	95.5	96	
	P-DD-ABS-10-48-W	119.5		
	P-DD-ABS-12-48-W	143.5		
	P-DD-ABS-16-48-W	191.5		

SwiftWall Pro Class C Series

Product Type	Product #	Height (in)	Width (in)	Thickness (in)
Panel	P-P-ABS-08-48-W	95.5	48	1.12
	P-P-ABS-10-48-W	119.5		
	P-P-ABS-12-48-W	143.5		
	P-P-ABS-16-48-W	191.5		
Window Panel	P-P-ABS-08-48-W-W	95.5		
	P-P-ABS-10-48-W-W	119.5		
	P-P-ABS-12-48-W-W	143.5		
	P-P-ABS-16-48-W-W	191.5		
Single Door Panel	P-DS-ABS-08-48-W	95.5		
	P-DS-ABS-10-48-W	119.5		
	P-DS-ABS-12-48-W	143.5		
	P-DS-ABS-16-48-W	191.5		
Double Door Panel	P-DD-ABS-08-48-W	95.5	96	
	P-DD-ABS-10-48-W	119.5		
	P-DD-ABS-12-48-W	143.5		
	P-DD-ABS-16-48-W	191.5		

SwiftWall Pro Accessories

Accessories work with Class C and Class A swiftwall Pro Series

Product Type	Product #	Length (in)
Track	P-T-10-W	120
C-Channel	P-CC-08-W	96
	P-CC-10-W	120
	P-CC-12-W	144
	P-CC-16-W	192
90 Degree Corner	P-C-08-W	96
	P-C-10-W	120
	P-C-12-W	144
	P-C-16-W	192
Adjustable Corner	P-CA-08-W	96
	P-CA-10-W	120
	P-CA-12-W	144
	P-CA-12-W	192
L Channel	P-LC-08-W	96
	P-LC-10-W	120
	P-LC-12-W	144
	P-LC-16-W	192


SwiftWall Pro Panel Weights

Weight of Pro Panels		
Height (ft)	ABS (lbs)	Aluminum (lbs)
4’	19.5	23.5
8’	29	47.5
10’	49	59.5
12’	58.5	71.5
16’	78	95

SWIFTWALL

SWIFTWALL® CLICK

SwiftWall Click is a game-changer in modular wall systems, offering a fast, reusable, and effortless solution for temporary walls and rooms



SwiftWall® Click has no tools or skills required. Designed for quick, flexible space solutions, its durable panels click together effortlessly without a bottom track or adjustable top trim. SwiftWall® Click is perfect for offices, events, trade shows, and more.

- **A simple temporary wall system that assembles in seconds**
- **Fastest temporary wall to install on the market**
- **Durable & lightweight - single person lift 35 lb. 8’ panel**

CLICK PANELS

Isolate and contain dust, separate and partition rooms, build entire events and more. Made of fire rated, non-hydroscopic swiftwall panels keep the noise down with an STC21 sound rating.

Standard panels are manufactured to a sturdy 4’ wide and 1” thick. Click panels come in heights of 8’ and 10‘. Panels easily join and lock together. Consult with a SwiftWall sales representative for more information.

Standard Sizes
8’
10’

Material
ABS with aluminum joiners and polyisocyanurate core (Class C Fire-Rated)
Matte painted aluminum skin with aluminum joiners and polyisocy-anurate core (Class A Fire-Rated)

Finish
Option 1: White light-sheeen matte hair-cell ABS
Option 2: Standard coated semi-gloss alu-minum (Class A Only)
Option 3: Powder coating upon request

SDS
Printed copies available upon request

Standard Panels



SWIFTWALL® PRO SWIFTWALL® MAX SWIFTWALL® FLEX SWIFTWALL® CLICK SWIFTWALL® LITE

SWIFTWALL®

SWIFTWALL CLICK

CLICK PARTS



Click Panels (Class A & C)



Door Panel



Window Panels



90 Degree Rounded Corner




Hinged Variable Angle Corner






T Joiner




X Joiner





End Caps: Provides a clean finish to the end panel run.




End Cap Kit

OPTIONAL PARTS



Track

Secures the panels along the floor for stabilization.



Double Sided Tape

Provides additional stability during installation.

SWIFTWALL PRO SWIFTWALL MAX SWIFTWALL FLEX SWIFTWALL CLICK SWIFTWALL LITE

SwiftWall Click 8’ Series

Product Type	Product #	Height (in)	Width (in)	Thickness (in)
Panel	C-P-ABS-08-48-W	95.5	48	1.12
	C-P-ABS-08-36-W		36	
	C-P-ABS-08-24-W		24	
	C-P-ABS-08-12-W		12	
36” x 36” Window Panel	C-P-ABS-08-48-W-W		48	
Single Door Panel	C-DS-ABS-08-KIT-W		48	
90 Degree Corner	C-C-08-W			
“T” Intersection Kit	C-T-08-KIT-W			
“X” Intersection	C-X-08-W			
End Cap Kit	C-EC-08-KIT-W			

SwiftWall Click 10’ Series

Product Type	Product #	Height (in)	Width (in)	Thickness (in)
Panel	C-P-ABS-08-48-W	119.5	48	1.12
	C-P-ABS-08-36-W		36	
	C-P-ABS-08-24-W		24	
	C-P-ABS-08-12-W		12	
36” x 36” Window Panel	C-P-ABS-08-48-W-W		48	
Single Door Panel	C-DS-ABS-08-KIT-W		48	
90 Degree Corner	C-C-08-W			
“T” Intersection Kit	C-T-08-KIT-W			
“X” Intersection	C-X-08-W			
End Cap Kit	C-EC-08-KIT-W			

SwiftWall Pro Accessories

Product Type	Product #
Mending Plate Kits	A-C-MP-SW
	A-C-MP-L
	A-C-MP-X
	A-C-MP-T
Click 6’ Brace	A-C-TB-6-W


SWIFTWALL

SWIFTWALL KITS

RECOMMENDED CONFIGURATIONS

20 LINEAR FOOT STRAIGHT WALL


Divide an Office Area | Create a Spare Basement Room | Create a Storage Space



Material List	Product #	Qty
SwiftWall Click Panel Class C - 4'w x 8'H - White	C-P-ABS-08-48-W	4
SwiftWall Click Single Door Panel Class C - 4'W x 8'H - LH Inswing - White w/Threshold and GR3 Handle Assembled (Door Handle & Spacer Included)	C-DS-ABS-08-KIT-W	1
Click End Cap Kit 95.5" T	C-EC-08-KIT-W	1
SwiftWall Click Mending Plate, Straight Wall, Kit	A-C-MP-SW	4
Sandwich Stand	P-SS-W	2

12' X 12' L-SHAPE WALL


Transform a Manufacturing Cell with a Barrier | Create Privacy in an Office



Material List	Product #	Qty
SwiftWall Click Panel Class C - 4'w x 8'H - White	C-P-ABS-08-48-W	5
SwiftWall Click Single Door Panel Class C - 4'W x 8'H - LH Inswing - White w/Threshold and GR3 Handle Assembled (Door Handle & Spacer Included)	C-DS-ABS-08-KIT-W	1
Click End Cap Kit 95.5" T	C-EC-08-KIT-W	1
SwiftWall Click Mending Plate, Straight Wall, Kit	A-C-MP-SW	4
Sandwich Stand	P-SS-W	2

12' X 12' ROOM


Create a Training Room | Divide Space for an Event



Material List	Product #	Qty
SwiftWall Click Panel Class C - 4'W x 8'H - White	C-P-ABS-08-48-W	10
SwiftWall Click Panel Class C - 4'W x 8'H - White with 36" x 36" Window	C-P-ABS-08-48-W-W	1
SwiftWall Click Single Door Panel Class C - 4'W x 8'H - LH Inswing - White w/Threshold and GR3 Handle Assembled (Door Handle & Spacer Included)	C-DS-ABS-08-KIT-W	1
SwiftWall Click 90-Degree Corner 8'L - White	C-C-08-W	4
SwiftWall Click Mending Plate, Straight Wall Kit	A-C-MP-SW	8
SwiftWall Click Mending Plate, L Corner Kit	A-C-MP-L	4
SwiftWall Click Top Brace, 6', White	A-C-TB-6-W	4

MULTI ROOM

Divide an Office Space | Create Private Changing or Sleeping Rooms



Material List	Product #	Qty
SwiftWall Click Panel Class C - 4'W x 8'H- White	C-P-ABS-08-48-W	20
SwiftWall Click Panel Class C - 2'W x 8'H- White	C-P-ABS-08-24-W	6
SwiftWall Click Single Door Panel Class C - 4'W x 8'H - LH Inswing - White w/Threshold and GR3 Handle Assembled (Door Handle & Spacer Included)	C-DS-ABS-08-KIT-W	4
Swiftwall Click 90-degree Corner 8'L - White	C-C-08-W	4
SwiftWall Click T Intersection Open Joiner 8' White	C-TO-08-W	2
SwiftWall Click T Intersection Closed Joiner 8' White	C-TC-08-W	2
SwiftWall Click X Intersection 8' White	C-X-08-W	1
SwiftWall Click Mending Plate, L Corner, Kit, Includes (4 drop-ins & thumb screws) per	A-C-MP-L	4
SwiftWall Click Mending Plate, T Intersection, Kit, Includes (6 drop-ins & thumb screws) per	A-C-MP-T	4
SwiftWall Click Mending Plate, X Intersection, Kit, Includes (8 drop-ins & thumb screws) per	A-C-MP-X	1
SwiftWall Click Mending Plate, Straight Wall, Kit, Includes (4 drop-ins & thumb screws) per	A-C-MP-SW	18
SwiftWall Click Top Brace, 6', White	A-C-TB-6-W	6
SwiftWall Click, mounting drop in kit, 1/4x20	A-C-MT-1/4X20	12

If you are looking for custom solutions, please contact our solutions team.
Call us at (989)279.0232 or Email us at sales@swiftwall.com

SWIFTWALL PRO SWIFTWALL MAX SWIFTWALL FLEX SWIFTWALL CLICK SWIFTWALL LITE

SWIFTWALL

SWIFTWALL®

TEMPORARY WALL SOLUTIONS

SwiftWall.com | 989.279.0232 | sales@swiftwall.com