
Souffle | E25055-CHK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

Deep pans of cast concrete in a traditional scalloped edge house LED integrated light sources behind curved opal white acrylic diffusers. Reminisce in the classical forms that benefits from the organic texture of cast concrete to add character to the design. Inspired by ramekins, these delectable LED treats are available in Chalk White, Terra Cotta, and Grey.



MEASUREMENTS

DIMENSION	: 33" L x 33" W x 3.25" H
MAX OAH	: 120" OAH
CANOPY	: 8.5" W x 1.25" H x 8.5" L
HANGING WEIGHT	: 9.45 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,280 Rated (2,900 Del.)
BULB	: 1 x 41W LED PCB Integrated , 41W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: TriacÂ orÂ ELVÂ atÂ 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Chaulk White (CHK)
Gray (GY)
Terra Cotta (TRC)

MATERIAL

Concrete, Steel, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com