Project / Job Name:

Location:

Fixture Type:

Notes:



S11846 - 5-6 inch; CCT Selectable; Integrated LED Recessed Downlight with Night Light Feature

GENERAL

Company	SATCO
EA Height	7.9
EA Width	8.5
EA Length	3.4
Bulb Included	Integrated
Diameter	7.4
Material	Aluminum
Fixture Type	Downlight Retrofit
Includes	E26 Adapter included (S9001)
Status	Active
Style	Utility
CCT Selectable	Yes
Wattage Selectable	No
Can Size	5-6 in.
Finish Family	White
Additional Info	Night Light emits 2200K 150L
Amps	0.075A
Has Camera	No
IOT Enabled	No
Lens Material	Polycarbonate (PC)
Power Factor	0.96
SDS Class	LED_Fixture
Sloped Ceiling Compatible	No
Indoor Outdoor	Indoor
Product Technology	LED
Incandescent Equivalent	65W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	2700K/3000K/3500K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	95
Color Temp	Warm to Cool White
CRI	90+
Dimming Type	120V only, Phase Cut (TRIAC)
Operating Frequency	60Hz
Operating Temp	-4F to +104F (-20C to +40C)
Lumens	800L
Volts	120v
Watts	9W
Connection	Connector or Adapter

PHYSICAL

Lamp Base	Medium Adapter
Finish	WHITE
ANSI Base	E26 Adapter
Lamp Type	Integrated LED
Fixture Shape	Round
Mounting Procedure	Ceiling

ADDITIONAL INFO

Warranty	5-Years

PACKAGING

UPC	045923118463
Case Cube	1.2291
Case Height	15.75
Case Length	15.94
Case Quantity	8
Case UPC	10045923118460
Case Weight	10.16
Case Width	8.46
EA Cube	0.1321
EA Height	7.9
EA Length	3.4
EA Quantity	1
EA Weight	1.15
EA Width	8.5
Pack Type	Box
Web Height	3.17
Web Width	7.4

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Certified, cULus - Classified
California Ban	California T24 Listed
DLC Approved	No
Energy Star Certified	No
Title 20	Yes
T24/JA8 Compliant	Yes

© Satco Products, Inc.
All rights reserved 2026