Project / Job Name:

Location:

Fixture Type:

Notes:



65-905 - 8 Foot; Quad Or Dual T8 Lamp Ready Fixture Channel; Empty Body Fixture; Complete Lamp Wiring Guide Available; White Finish

GENERAL

Company	NUVO
EA Height	4.33
EA Width	5.11
EA Length	49.2
Bulb Included	No
Material	Steel
Fixture Type	Linear
Status	Active
Style	Utility
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Amps	0.075-0.026A
Nominal Length	48.0
Product Technology	LED
Fixture Lamp Count	4
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

Operating Frequency	50/60Hz
Volts	120V-347V
Watts	660W
Connection	Hardwire

PHYSICAL

Lamp Base	Miniature 2 Pin Round Adapter
Finish	WHITE
ANSI Base	Bi-Pin Adapter
Lamp Type	T8

ADDITIONAL INFO

Warranty	1-Year

PACKAGING

UPC	045923409905
Case Cube	3.0005
Case Height	9.64
Case Length	49.8
Case Quantity	4
Case UPC	10045923409902
Case Weight	40.34
Case Width	10.8
EA Cube	0.63
EA Height	4.33
EA Length	49.2
EA Quantity	1
EA Weight	9.24
EA Width	5.11
Pack Type	Kraft Box
Web Height	3.62
Web Length	48.46
Web Width	4.6

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	No
Location Rating	Damp
NSF Approved	No
ROHS Compliant	No
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026