Pearl | E24075-BKNAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

An artistic and flexible design concept, crystal orbs are illuminated behind curved Naturally Aged Brass shades. The oversized panes are mounted to LED light housings that can rotate to provide either ambient indirect lighting that is directed upwards at the crystal for a glowing effect, or these LEDs can be rotated to shine downward for ample lighting. The two-arm wall sconce has a longer extension in the arm with individual light switches on the backplate to be used for directed task lighting great for bedside applications or creating a space within a room that will serve as task lighting.



MEASUREMENTS

DIMENSION	: 47.25" L x 47.25" W x 22" H
MAX OAH	: 65.25" OAH
CANOPY	: 6.25" W x 1.25" H x 6.25" L
HANGING WEIGHT	: 14.3 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 3,600 Rated (1,850 Del.)
BULB	: 6 x 6W LED PCB Integrated , 36W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Directional

FINISHES OPTION

Black / Natural Aged Brass (BKNAB)

MATERIAL

Steel, Aluminum, Crystal

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com