



TEGERA® 825A

Learn more

WHEN YOU NEED A SMOOTH FINISH

A thin, disposable PVC (Vinyl) glove with a natural fit, ESD protection, and a smooth finish. It is ideal for applications such as food preparation, light-duty cleaning, and general maintenance. It offers touchscreen functionality, so there's no need to take the gloves off when using your smartphone. Thickness: 0,10 mm/3,9 mils. Additionally, it is latex-free. 100 pieces/box. 10 boxes/carton.

CHARACTERISTICS

- Flexible

FUNCTIONS

- For touchscreen
- Latex-free
- ESD
- Waterproof
- Conforms with IEC 61340-5-1 (ESD)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF
Risk of infection, Contact with moisture, Contact with damp

PRIMARY ENVIRONMENTS OF USE
Microbiological risk environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE
Assembly, Care work, Cleaning, Decontamination, Fine assembly, Food handling, Healthcare, Hotel- and restaurant work, Kitchen work, Sanitation, Service work

PRIMARY INDUSTRIES OF USE
Food and beverage processing, Public safety, security and defence, Accommodation and food service (HoReCa)

TYPE OF WORK
Light weight

CHEMICAL RESISTANCE
According to EN16523-1:2015. For details, please contact Ejendals.

SPECIFICATION
TYPE Disposable gloves - General protection, ESD gloves
CATEGORY Cat. III
THICKNESS 0,10 mm
LENGTH 240 mm
INSIDE Non powder
COLOUR Colourless
QUANTITY PER PACK 100 Pieces
PACKS PER: BUNDLE/CARTON Not sold in bundle/10
AQL 1.5
DISPLAY TYPE Box
DIPPING MATERIAL PVC (Vinyl)
CUFF STYLE Rolled edges

COMPLIANCE
CE 2777 — TP TC 019:2011

UKCA Cat. III — EN ISO 21420:2020

EAC

EN ISO 374-5:2016 Virus

EN ISO 374-1:2016+A1:2018 Type B
KPT

NOT FOR FATTY FOOD

FDA compliant material

IEC 61340-5-1:2016
R < 1.0 x 10⁹ Ω

FEATURES
General Protection

For touchscreen

Waterproof

TEST ACCORDING TO EN ISO 374-1:2016

Tested chemical	K	P	T
Permeation level	6	6	5
Degradation %	9,1	-25,6	-2,6

SIZE		ARTICLE NUMBER	EAN
7	S	825A-7	7340118352749
8	M	825A-8	7340118352831
9	L	825A-9	7340118352923
10	XL	825A-10	7340118353012

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.