

A high-quality neoprene disposable splash protection glove. Structured fingertips.

TEGERA® CHEMFORCE 837

Learn more

EXTRA-LONG FOR EXTRA PROTECTION

A high quality, comfortable, extra-long 0,12 mm/4,7 mil neoprene disposable glove. Structured fingertip and powder free. Suitable glove for work in areas where there is a risk of chemical splashes. Good grip, good fit and touchscreen functionality. Use your smartphone with the gloves on. 100 pieces/box. 10 boxes/carton.

CHARACTERISTICS

- Good fingertip sensitivity
- Extra flexible
- Very durable
- Good grip
- Good fit
- Light

FUNCTIONS

- Splash protection against chemicals
- For touchscreen
- Extra long
- Waterproof
- Soft
- Elastic

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Contact with chemicals, Contact with moisture, Contact with damp, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Chemical risk environments, Disposable use

PRIMARY AREAS OF USE

Fine assembly, Chemical technology work, Laboratory work

PRIMARY INDUSTRIES OF USE

Metal manufacturing and fabrication, Transport equipment manufacturing, Food and beverage processing, Chemical and petrochemical industry, Machinery and equipment manufacturing, Automotive manufacturing, Public safety, security and defence

TYPE OF WORK

Light weight

CHEMICAL RESISTANCE

According to EN16523-1:2015. For details, please contact Ejendals.

SPECIFICATION

TYPE Chemical protection gloves, Disposable gloves - Chemical splash protection
CATEGORY Cat. III
COLLECTION Chemforce
THICKNESS 0,12 mm
LENGTH 290 mm
DEXTERITY 5
INSIDE Non powder
GRIP DESIGN Extra fingertip grip
COLOUR Green
QUANTITY PER PACK 100 Pieces
PACKS PER: BUNDLE/CARTON Not sold in bundle/10
AQL 1.5
DISPLAY TYPE Box
DIPPING MATERIAL Neoprene

COMPLIANCE

CE 2777

EAC

TP TC 019:2011

EN ISO 21420:2020

EN ISO 374-5:2016 Virus

EN ISO 374-1:2016+A1:2018 Type B KPT

EN 421:2010

FDA compliant material

FEATURES

Chemical splash protection

For touchscreen

Waterproof

TEST ACCORDING TO EN ISO 374-1:2016

Tested chemical	K	P	T
Permeation level	6	6	6
Degradation %	4,6	4,8	2,1

SIZE		ARTICLE NUMBER	EAN
7	S	837-7	7340118303819
8	M	837-8	7340118303833
9	L	837-9	7340118303857
10	XL	837-10	7340118303772

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.