

EVAN

B4716-PBR

Combining geometric shapes and three distinctive earthy materials, the Evan sconce generates its own visual design language. The design -forward composition includes a swooping J-arm in Patina Brass, leading into an overscale walnut wood bobèche. As a note of contrast, the fixture is topped by a sharply tapered shade made from grained white linen.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 16"

Width/Diameter: 11.75"

Canopy/Backplate: 4.75"

Product Weight: 2.5lb

Extension: 12.5"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

Shade 1: Fabric

Shade 1 Finish: Textured Linen

Shade 1 Top Width: 2"

Shade 1 Bottom L/W: 0" / 11.75"

Shade 1 Height: 5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A15

Max Wattage: 10

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 21" x 16" x 10"

Carton 1 Weight: 5lb

Shipping Method: Ground

Country of Origin: VN

