
Manta | E24712-144GLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION

An undulating shape softly curls along its center to create an organic form constructed of a single panel of transparent acrylic. Further enhancing the form is the captivating effect of the frosted band around the borders and the patterned etching on the acrylic that captures the light. A coordinating wall sconce that features the same curled acrylic material and extends only 4 inches from the wall for ADA compliant applications.



MEASUREMENTS

DIMENSION	: 24.75" L 6.75" H x 5.5" Ext
MAX OAH	:
CANOPY	: 4.75" W x 1.5" H x 4.75" L
HANGING WEIGHT	: 4.1 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,440 Rated (900 Del.)
BULB	: 1 x 20W LED DC Integrated , 20W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Black (BK)
Gold (GLD)
Polished Chrome (PC)

GLASS

Clear Ribbed 144

MATERIAL

Aluminum, Steel, Acrylic

RATINGS

cETLus
Damp Location

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com