



Ironcat®

AR Premium Top Grain Goatskin Leather MIG Welder's Glove with Split Cowhide Back and Para-Aramid Liner

- Top Grain Goatskin leather construction is the softest, most abrasion-resistant leather and is highly recommended for applications requiring tactile sensitivity
- Top Grain leather is smooth, provides durability and dexterity
- Split Cowhide leather back provides comfort, durability, excellent abrasion resistance, and breathability
- Gunn cut pattern delivers excellent durability, wear and comfort, especially for heavier gloves
- Reinforced thumb crotch strap for extended glove life, enhanced comfort, increased abrasion resistance and added durability in a high-wear area
- Straight thumb increases comfort in closed-fisted work
- Stitched with Kevlar® adding strength and burn resistance
- Para-Aramid blend 360 degree lining provides added cut and heat resistance
- ARC Rating: ATPV 20 cal/cm2
- Brown split cowhide gauntlet cuff for added forearm protection and allows for easy on and off



Technical Data

Color	Brown
Sizes Available	S-2XL
Packaging	Bulk Pack
Packed	6 Dozen/Case
Case Dimensions (in)	19.53 x 15.98 x 19.02
Case Weight (lbs)	48.88
Country of Origin	Pakistan
Hide	Top Grain Goatskin
Lining	Fleece Pile
Grade	Premium
Cuff	Gauntlet
Length	12"
Palm	Leather
Back	Leather
Closure	Slip On
Thumb	Straight
Stitching	Kevlar
Construction	Cut-and-Sewn, Gunn Cut
Certifications	Chromium VI Free

Performance Data

ARC Rating	20 cal/cm2
ARC Rating	20 cal/cm2
Cut Level	A4
Cut Level	A4
ANSI Puncture Level	3
ANSI Puncture Level	3

Care Instructions



Do Not Wash

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
6243/S	Brown	S	616314368042	10616314368049	20616314368046
6243/M	Brown	M	616314375675	10616314375672	20616314375679
6243/L	Brown	L	616314369339	10616314369336	20616314369333
6243/XL	Brown	XL	616314375712	10616314375719	20616314375716
6243/2XL	Brown	2XL	616314368004	10616314368001	20616314368008