



YA29L4, Comp Term, 1 Hole, 3/8 Stud, Std, Inspection Window

By Burndy
Catalog # [YA29L4](#)

250 kcmil, CU, 1 Hole, 3/8 Stud, Standard Barrel, Inspection Window, Tin Plated

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper DLO Size Range	N/A
Conductor Size	250 KCMIL
Conductor - Copper Str Navy Size Range	250 (61) Navy
Conductor - Copper Str Navy Size	250 (61) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	250 kcmil

Configuration



Physical Attribute - Number of Holes	1
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.11 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	61 mm
Dimension - Outside Diameter inch	0.75 in
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/16 in
Dimension - Z inch	0.42 in
Dimension - B Length inch	1.06 in
Dimension - D inch	0.83 in
Dimension - N inch	0.41 in
Dimension - Bolt Size inch	0.38
Dimension - Length Overall inch	2.42 in

General

Trade Name	HYLUG™
Die Index	16
Feature - Barrel Type	Standard
Feature - Barrel Style	• Chamfered • Skived
Plated	Y
Color Code	Yellow

Physical Attribute - Tongue	Standard
Type	
Sub Brand	HYLUG
UPC	781810554524
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 14 Digit GTIN	00781810554524

Logistics

Minimum Pack Quantity	1
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand