
Alumilux Bollard | E41453-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____



PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 8" W x 21.25" H
HANGING WEIGHT	: 1.98 lb

LAMPING

INPUT VOLTAGE	: 12V
LUMENS	: 490 Rated (260 Del.)
BULB	: 1 x 7W LED DC Integrated , 7W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: N
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com