

VIOLETTA

H1126102-AGB

Defined by clean design and sculptural symmetry, the Violetta sconce balances linearity with artistry. Two cream opal glass shades are stacked, divided by a slim Aged Brass band that introduces a moment of contrast. With restrained geometry, Violetta makes a confident statement on the wall.

FINISHES

AGED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 18"

Width/Diameter: 4.75"

Length: 3.5"

Canopy/Backplate: 4.75"

Product Weight: 3lb

Extension: 3.5"

Top to Center: 10.75"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Cream Opal Glossy

Shade 1 Top Width: 2.75"

Shade 1 Height: 9"

Shade 2: Glass

Shade 2 Finish: Opal Glossy

Shade 2 Top Width: 2.75"

Shade 2 Height: 5.75"



ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: T10-9

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

Bulb 2

Bulb Included: No

Socket: E26 Medium Base

Bulb: T10-5.5 • 1 • 15 Watt Max

Voltage: 120V

UL Rating: cUL Damp

Gem Box: Not Required

SHIPPING

Carton 1: 12" x 7" x 13"

Carton 1 Weight: 5lb

Shipping Method: Ground

Country of Origin: VN