



WNL033I



3.75" x 24" x 20" (H x W x D)

24" wide gas cooktop in white with 4 open burners, continuous cast iron grates, and spark ignition, made in the USA

Highlights:

- Made in the USA
- 24" size fits popular 22 5/8" W x 18 5/8" D counter cutouts
- Premium cast iron grates hold up to heavy duty cookware

Product Features:

24" Wide Gas Cooktop	Built-in natural gas cooktop with four open burners
Made in the USA	Designed and constructed domestically
Cast iron grates	Two sets of continuous grates in heavy duty cast iron hold up to large cookware
Classic 24" size	Fits common 22 5/8" W x 18 5/8" D counter cutouts
Four open burners	9000 BTU burners meet most cooking needs
White exterior	Classic design in a clean white finish to match any kitchen
Porcelain finish	Scratch-resistant design for lasting durability
Recessed top	Curved design helps to contain spills on the surface
Electronic/gas spark ignition	Spark ignition system with a pre-installed 115V cord and standard NEMA 5-15P plug



WNL033I Specifications:

Overview	
Nominal Height	4.0" (10 cm)
Height of Cabinet	3.75" (10 cm)
Nominal Width	24.0" (61 cm)
Width	24.0" (61 cm)
Nominal Depth	20.0" (51 cm)
Depth	20.0" (51 cm)
Cabinet	White
US Electrical Safety	CSA
Voltage/Frequency	115 V AC/60 Hz
Weight	27.0 lbs. (12 kg)
Parts & Labor Warranty	1 Year
UPC	761101158204
Gas Cooktop	
Ignition	Spark
LP Convertible	With Kit LP Accessory
Number of Burners	4
Controls	Dial
Surface	Painted
Grate Material	Cast Iron
Cutout Width	22.63" (57 cm)
Cutout Depth	18.63" (47 cm)
Burner #1 BTU	9000.0
Burner #2 BTU	9000.0
Burner #3 BTU	9000.0
Burner #4 BTU	9000.0
Power Cord Included	Yes

