# **Reeds** | E11019-144BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








## PRODUCT DESCRIPTION

A refined play of texture and proportion, this series juxtaposes vertically fluted aluminum housings with linear reeded glass tubes. Offered in Gold or Matte Black finishes, each form integrates frosted glass diffusers that soften the powerful LED illumination within. Designed for architectural flexibility, the collection includes ADA-compliant sconces, a minimalist stem-hung GU10 pendant, adjustable GU10 spotlights, and an additional flush mount. Universal dimming and commercial-grade drivers make it ideal for elevated residential, hospitality, or decorative commercial settings.




*max overall height

### MEASUREMENTS

| | |
|---|---|
| DIMENSION | : 20.75" L x 20.75" W x 17" H |
| MAX OAH | : 137" OAH |
| CANOPY | : 19.5" W x 1.5" H x 19.5" L |
| HANGING WEIGHT | : 34.2 lb |

### LAMPING

| | |
|---|---|
| INPUT VOLTAGE | : 120-277V |
| LUMENS | : 4,800 Rated (2,880 Del.) |
| BULB | : 12 x 5W LED PCB Integrated , 60W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : 3-in-1: Triac, ELV, or 0-10V |
| CRI | : 90 CRI |
| COLOR_TEMP | : 3000K |

### FINISHES OPTION

Black (BK)
Gold (GLD)

### GLASS

Clear Ribbed 144

### MATERIAL

Steel, Aluminum, Glass

### RATINGS

cETLus
Dry Location

### ADDITIONAL

SLOPE: 30
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com