

# YS36, Cu Compression Splice, Long Barrel, 600 kcmil

By Burndy  
Catalog # [YS36](#)



600 kcmil, CU, Long Barrel SPLICE

## Features

- Copper seamless barrel with center stop indentations to indicate when wire is fully inserted into each side of the barrel
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

## Application

Wire Splice

## Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

## Conductor

Conductor - Material	COPPER
Wire Size	600 kcmil
Conductor - Copper Str Size	600 kcmil
Conductor Size	600 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	600 kcmil

## Configuration

Connector Type	LONG BARREL
----------------	-------------

## Current

Voltage Rating	35 kV
Voltage - Maximum	35000

## Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	149 mm
Dimension - Strip Length inch	2-11/16
Dimension - B Length inch	2.63 in
Dimension - Length Overall inch	5.85 in

## General

Trade Name	HYLINK™
Die Index	22
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Green
Sub Brand	HYLINK
UPC	781810526255
Type	YS, Long Barrel
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810526255
UPC 14 Digit GTIN	00781810526255

## Logistics

Minimum Pack Quantity	1
Carton Quantity	6

## Product Assets

[Catalog \[English\]](#)