

## Watertight Devices, Twist-Lock® Plug, 20A, 3 Phase 250V AC, 3 Pole, 4 Wire, Thermoplastic elastomer, NEMA L15-20P, Yellow

By Hubbell Wiring Device-Kellems  
Catalog # [HBL26W75](#)

PLUG, W/TIGHT, 3P 20A 250V, L15-20P, YL

### Features

- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection
- Stainless steel hardware and corrosion-resistant connection points

### Performance

Electrical - Current Interrupting - Rated for current interruption per UL498, Electrical - Dielectric Voltage - 2500V AC, Electrical - Max Working Voltage - As marked, Electrical - Temperature Rise - 30°C max per UL498 at rated current, Environmental - UV resistance - All exposed materials are UV stabilized, Environmental - Moisture Resistance - UL Listed 4, 4X, 12, 6, 6P, Environmental - Operating Temperatures - -40°C (without impact) to +60°C continuous, Mechanical - Cord Accommodation - 0.375"-0.875" (9.5-22.2)

### Specifications

Nema Rating	L15-20P
Standards - RoHS Compliance Status	CM
Industry Standard(s)	Meets NEMA WD-1, WD-6 And ANSI Standards
EU RoHS Indicator	Contact Manufacturer

### Conductor

Number Of Poles	3-Pole
Number Of Wires	4-Wire



### Wire Size

- Min. Cord: 16/3 SJ, 18/3 S, 18/4 SJ, 18/4 S, 18/5 S
- Max. Cord: 10/3 S, 10/4 S, 10/5 S

### Current

Amperage Rating	20 A
Voltage Rating	3 Phase 250 VAC
Voltage Rating Description	3 Phase 250 VAC
Current / Amperage Rating	20 A

### Dimensions

Height	3.96 in
Width	2.51 in
Length	2.51 in
Dimensions	2.51 in x 2.51 in x 3.96 in

### General

Color	Yellow
UPC	783585131634
Type	Plugs
Item Type	20A Watertight Twist-Lock® Plug

### Logistics

Pallet Quantity	960
Carton Quantity	10

### Product Assets

[Catalog \[English\]](#)