



Project / Job Name:

Location:

Fixture Type:

Notes:

65-1284 - Momentum; X-Connector for LED Linear System; Black Finish



GENERAL

Company	NUVO
EA Height	7.87
EA Width	4.33
EA Length	7.87
Material	Aluminum
Status	Active
CCT Selectable	Yes
Finish Family	Black
Amps	0.200A
Lens Finish	White
Lens Material	Polycarbonate (PC)
Lensed	Yes
Product Technology	Not Applicable

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	120
Color Temp	Soft White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-4F to +113F (-20C to +45C)
Lumens	750L
Watts	6.6W

PHYSICAL

Finish	BLACK
--------	-------

ADDITIONAL INFO

Warranty	5-Years
----------	---------

PACKAGING

UPC	045923654350
Case Cube	1.1264
Case Height	13.78
Case Length	16.54
Case Quantity	6
Case UPC	10045923654357
Case Width	8.54
EA Cube	0.1552
EA Height	7.87
EA Length	7.87
EA Quantity	1
EA Width	4.33
Pack Type	Box
Web Height	3.4
Web Length	5.8
Web Width	5.8

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
Location Rating	Damp
ROHS Compliant	Yes
Safety Listing	cETLus - Listed
California Ban	Lawful for sale
Title 20	Exempt
T24/JA8 Compliant	No