

MARCO

B6218-PBR

An elevated globe sconce, Marco combines curved glass and angular metalwork to create a modern, distinctive look for the outdoors. The lantern-style hanging design features a large, clear glass orb suspended from minimalist industrial fittings. Within the shade, a ribbed glass tube conceals the light source while adding a dynamic geometric layered effect. Marco is available in two sizes with Patina Brass or Bronze finish options.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 18.25"

Width/Diameter: 13"

Canopy/Backplate: 5.5"

Product Weight: 5.5lb

Extension: 13.75"

Top to Center: 2.75"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: Yes

Uplight Only: Yes

Shade

Shade 1: Glass

Shade 1 Finish: Clear Inside Etched

Shade 1 Top Width: 3.5"

Shade 1 Height: 13.25"

Shade 2: Glass

Shade 2 Finish: Clear

Shade 2 Top Width: 13"

Shade 2 Height: 13.25"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: T10-9

Max Wattage: 15

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 17" x 17" x 21"

Carton 1 Weight: 10lb

Shipping Method: Ground

Country of Origin: VN

