

CLARISSE

H1132703-AGB/SBQ

A classic lantern shape is reimagined with the spirit of modern romance. The hexagonal frame of Clarisse features arched glass panels that reveal cream candles. With a mix of Aged Brass and either Soft Bisque or Arctic Ocean finishes, each lantern is a festive celebration of color. Available as a small 3-light or large 4-light design.

FINISHES

AGED BRASS w/ SOFT BISQUE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 22.25"

Width/Diameter: 13"

Minimum Height: 26"

Maximum Height: 62"

Canopy/Backplate: 4.75"

Hanging Type: 54" Chain, 1-3" / 1-6" / 1-12" / 1-18"
Stems

Product Weight: 10lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear

Shade 1 Top Width: 6"

Shade 1 Bottom L/W: 0" / 3"

Shade 1 Height: 13.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 3

Wire Length: 120"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 16" x 16" x 20"

Carton 1 Weight: 13lb

Shipping Method: Ground

Country of Origin: VN

