
Soleil | E24983-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Sweeping matte white acrylic tubes encase an omnidirectional LED light source, arranged in abstract configurations inspired by solar flares. Minimal in composition yet dramatic in form, the Soleil collection offers a striking lighting solution. Available in a range of sizes, including fixed flush mount and field-adjustable pendant configurations, Soleil is offered in Polished Chrome, Matte Black, and Natural Aged Brass, making it a perfect complement to a variety of interior color schemes.



*max overall height

MEASUREMENTS

DIMENSION	: 13" L x 13" W x 29.25" H
MAX OAH	: 152.75" OAH
CANOPY	: 13" W x 1.5" H x 13" L
HANGING WEIGHT	: 8.8184 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,000 Rated (2,700 Del.)
BULB	: 3 x W LED DC Integrated , 45W Total
BULB INCLUDED	: (Integrated)
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

- Black (BK)
- Natural Aged Brass (NAB)
- Polished Chrome (PC)

MATERIAL

Steel, Aluminium

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 20000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com