Inverter (Vector) Duty Motors

Model No: LM04003
Catalog No: LM04003

Inverter (Vector) Duty Motor, 5 HP, 3 Ph, 60 Hz, 230/460 V, 1800 RPM, 213TC Frame, TENV

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: LM04003, Catalog No: LM04003 Inverter (Vector) Duty Motor, 5 HP, 3 Ph, 60 Hz, 230/460 V, 1800 RPM, 213TC Frame, TENV

Nameplate Specifications

Phase	**3**	Output HP	**5 Hp**
Output KW	**3.7 kW**	Voltage	**230/460 V**
Speed	**1760 r/min**	Synchronous RPM	**1800 r/min**
Service Factor	**1.00**	Frame	**213TC**
Enclosure	**Totally Enclosed Non Ventilated**	Thermal Protection	**Thermostat**
Efficiency	**82.5 %**	Ambient Temperature	**40 °C**
Frequency	**60 Hz**	Current	**15.6/7.8 A**
Power Factor	**73**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**INV**
KVA Code	**L**	Drive End Bearing Size	**6208**
Opp Drive End Bearing Size	**6206**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**43**	Number of Speeds	**1**

Technical Specifications

Electrical Type	**Squirrel Cage Inverter Duty**	Starting Method	**Inverter Only**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**2 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Aluminum**
Shaft Type	**T**	Overall Length	**21.14 in**
Frame Length	**8.0 in**	Shaft Diameter	**1 3/8 in**
Shaft Extension	**3.38 in**	Assembly/Box Mounting	**F1/F2 Capable**
Inverter Load	**Constant 100:1**		

Drawings

Connection Drawing	**EE7308T**	Outline Drawing	**SS330213LN-800**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 14/10/2026