Echo | E51012-WTGLD


Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____





PRODUCT DESCRIPTION

Surrounded by a metal drum shade in a variety of sizes and finishes, an internal shade constructed of acrylic evenly diffuses bright LED illumination. Designed for simpler installation and in an aesthetically pleasing silhouette, these practical metal drum shades are offered in Matte White both inside and out, or enhanced by gold or black interiors for reduced glare and stylish design. The series also features a chic Black with Gold interior color combination shade. To round out the collection, all these color options are also made compatible with a pendant accessory that quickly converts the flush mount fixtures into drum shade pendants.



MEASUREMENTS

DIMENSION	: 16" L x 16" W x 4.25" H
HANGING WEIGHT	: 7.9 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,000 Rated (1,500 Del.)
BULB	: 1 x 25W LED DC Integrated , 25W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac / 0-10V
CRI	: 90 CRI
COLOR_TEMP	: Select 27-50KK

FINISHES OPTION

- Black / Gold (BKGLD)
- White (WT)
- White / Black (WTBK)
- White/Gold (WTGLD)

MATERIAL

Aluminum, Polycarbonate

RATINGS

cETLus
Damp Location
CA Title 24

ADDITIONAL

OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com