



<b>EAN:</b>	4013288120090	<b>Size:</b>	90x44x20 mm
<b>Part number:</b>	05003508001	<b>Weight:</b>	23 g
<b>Article number:</b>	8790 HMA	<b>Country of origin:</b>	TW
		<b>Customs tariff number:</b>	82042000

- 1/4" Zyklop socket
- For manual and power tool operations (non-impact)
- Knurling at lower end to enable easy gripping when used in manual applications
- Equipped with ball stop groove
- With Take it easy tool finder: colour coding by size

The Wera manual and machine socket (ISO 2725 part 3) can be used in manual and machine operations. With Take it easy tool finder with colour coding by size - for quick and easy identification of the required tool. Slip-proof for easy grip even with oily hands. With ball stop groove. For external hexagon screws and bolts. Made of matte chrome-plated chrome-vanadium.

**Web link**  
<https://www.wera.de/en/05003508001>

Wera - 8790 HMA  
05003508001 - 4013288120090

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

### Take it easy tool finder system

### Manual and machine sockets



Nutsetter for hexagon head screws



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklus bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklus sockets and Zyklus bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklus bit sockets).



The manual and machine sockets can be used both for hand and power tools use (non-impact). Users need just one socket set for all applications.

#### Web link

<https://www.wera.de/en/05003508001>

Wera - 8790 HMA

05003508001 - 4013288120090

Wera Werkzeuge GmbH







Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

## Further versions in this product family:

							
		mm	inch	mm	mm	mm	mm
05003501001	violett_2735C	4.0	-	23.0	6.9	13.0	10.0
05003502001	rot_200C	4.5	-	23.0	7.5	13.0	10.0
05003503001	leuchtgruen_37 5C	5.0	-	23.0	8.2	13.0	10.0
05003504001	leuchtorange_1 52C	5.5	-	23.0	8.8	13.0	10.0
05003505001	blau_307C	6.0	-	23.0	9.4	13.0	10.0
05003506001	gelb_123C	7.0	-	23.0	11.0	13.0	10.0
05003507001	leuchtpink_232 C	8.0	-	23.0	12.0	13.0	10.0
<b>05003508001</b>	<b>gruen_363C</b>	<b>9.0</b>	<b>-</b>	<b>23.0</b>	<b>13.0</b>	<b>14.0</b>	<b>10.0</b>
05003509001	leuchtgelb_yello wC	10.0	-	23.0	14.5	14.5	-
05003510001	cyan_2985C	11.0	-	23.0	16.0	15.0	13.0
05003511001	schwarz_blackC	12.0	-	23.0	17.0	16.0	13.0
05003512001	tuerkis_339C	13.0	-	23.0	18.0	17.0	13.0
05003513001	pink_241C	14.0	-	23.0	20.0	18.0	13.0
05003499001	weiss	15.0	-	23.0	21.5	19.0	13.0
05003514001	leuchtorange_1 52C	-	3/16"	23.0	7.5	13.0	10.0
05003515001	cyan_2985C	-	7/32"	23.0	8.8	13.0	10.0
05003516001	leuchtgelb_yello wC	-	1/4"	23.0	11.0	13.0	10.0
05003517001	leuchtpink_232 C	-	9/32"	23.0	11.0	13.0	10.0
05003518001	blau_307C	-	5/16"	23.0	12.0	13.0	10.0
05003519001	leuchtgruen_37 5C	-	11/32"	23.0	13.0	14.0	10.0
05003520001	rot_200C	-	3/8"	23.0	14.5	14.5	-
05003521001	violett_2735C	-	7/16"	23.0	16.0	15.0	13.0
05003522001	tuerkis_339C	-	1/2"	23.0	18.0	17.0	13.0
05003523001	pink_241C	-	9/16"	23.0	20.0	18.0	13.0

## Web link

<https://www.wera.de/en/05003508001>

Wera - 8790 HMA

05003508001 - 4013288120090

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de