



TEGERA® INFINITY 8810

Learn more

SUPER SOFT WINTER GLOVE, PALM DIPPED.

Winter lined glove with super soft nitrile foam palm dipping for the cold season or in cool work areas. Designed for versatile work in dry to semi-dry environments. It is warm and comfortable but still soft and flexible with the high dexterity and fingertip sensitivity that is unique for an Infinity glove. Breathable materials for all day comfort. Skin friendly with Derma-test and Oeko-Tex certificate.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Extra comfortable
- Warm

FUNCTIONS

- Withstands contact heat up to 100°C
- Approved for handling foodstuffs

STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Dry environments, Cold environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Machine operating, Building and construction, Carpentry, Installation work, Construction, Transport work, Machine driving, Warehouse work, Airport work, Repair work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Agriculture, forestry and fishing, Facility management services, Basic metals manufacturing, Transportation and logistics, Electricity and gas supply, Building and construction, Mining and quarrying, Warehousing, Public safety, security and defence, Retail and wholesale

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cold insulation gloves, Heat protection gloves
CATEGORY Cat. II
COLLECTION Infinity
LINING Winter-lined
KNITTING GAUGE (GG) 10, 15
LINING MATERIAL Acrylic, Fleece, Nylon, Spandex
LENGTH 235-275 mm
DEXTERITY 5
GRIP DESIGN Foam grip pattern
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL Nitrile foam, Waterbased PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level A
CUT RESISTANCE (EN ISO 13997) TDM: 8 N
INNER MATERIAL SPECIFICATION Acrylic, Nylon
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 4221A

EN 407:2020 (No flame protection) X1XXXX

EN 511:2006 X2X

ANSI 5 ABR

Contact heat rating valid for palm area only

FEATURES

Warm lining

SIZE		ARTICLE NUMBER	EAN
7	S	8810-7	7340118321424
8	M	8810-8	7340118321448
9	L	8810-9	7340118321462
10	XL	8810-10	7340118321363
11	XXL	8810-11	7340118321387

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.