

Product information

Marine Winch Grease

PI 24/09/15/2026



Description

A synthetic high-performance grease enhanced with solid PTFE solid-lubricants. Specifically developed for use on winches and hoists. The solid lubricant provides the ultimate in wear protection and friction reduction. Resistant to seawater and freshwater and with excellent adhesive properties. Does not contain resins or acids and does not affect non-ferrous metals or plastics. Certification DIN KHCF1N-35.



Properties

- outstandingly adherent
- excellent high-pressure and wear protection properties
- outstanding sea and salt water resistance
- ensures a long service life

Technical data

Brief description	KHCF1N-35
Thickener	gel
Base	synthetic oil
Operating temperature range	-35 - +302 °F
Color / appearance	white
NLGI number	1
	DIN 51 818
Dropping point	without
	DIN ISO 2176
Base oil viscosity 104 °F	380 mm ² /s
	DIN 51 562
resistance to water washout	0
	DIN 51807

Areas of application

Particularly suited for winches and hoists with non-ferrous metal pairings and plastic/metal pairings. Saltwater resistant.

Application

Observe the manufacturers instructions!

Available pack sizes

100 g Tube plastic	20524
	CAEN-CAFR-USEN

Our information is based on thorough research and may be considered reliable, although not legally binding.