Hover | E21377-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Minimalist batons of extruded Black aluminum are fitted with V shaped acrylic diffusers for a wider beam of light. They can be arranged in numerous configurations allowing creativity and design of your own unique sculpture.



*max overall height

MEASUREMENTS

DIMENSION	: 18.25" L x 18" W x 18.25" H
MAX OAH	: 140.5" OAH
CANOPY	: 18" W x 1.5" H x 18" L
HANGING WEIGHT	: 9.5 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,000 Rated (2,000 Del.)
BULB	: 8 x 51W LED PCB Integrated , 51W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Only at 120V with ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

MATERIAL

Steel + Aluminum + Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com