



Ironcat®

FR Treated 100% Cotton Sateen Sleeves with 3/4" Elastic Ends

- FR treated 9 oz. 100% cotton sateen fabric offers protection in low heat and light spark applications
- Blousy fit to protect from an open flame or high heat applications
- 3/4" elastic ends provides a comfortable, snug fit and helps eliminate debris from entering the sleeve
- Certified to ISO 11611, ISO 11612, ASTM D6413

Technical Data

Color	Green
Sizes Available	18"-23"
Packaging	Bagged Each
Packed	72 Pair/Case
Case Dimensions (in)	19.70 x 17.70 x 17.70
Case Weight (lbs)	18.10
Clothing Type	Sleeves
Fabric	Sateen
Weight	9oz
Closure	Elastic
Certifications	ASTM D6413, TAA Compliant
Product Circularity	Reusable / Launderable

Care Instructions



Machine Wash



Water Temp 60°C



Do Not Bleach



Tumble Dry



Low Heat



Dry-clean

Failure to launder properly could adversely affect the flame resistance of the fabric.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
7071/18	Green	18"	662909004659		10662909004656
7071/23	Green	23"	662909004666		10662909004663