Alcove | E30104-BKGLD

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Die cast aluminum frames house a niche ofÂ stainless steel corrugatedÂ panelsÂ in a Gold finish. Two strips of dedicated LED lighting illuminate the washboard shape, which produces a warmer ambient light source when reflected off theÂ contrasting Gold tone.



MEASUREMENTS

DIMENSION	: 6.5" W x 14" H x 2.5" Ext
BACK PLATE	: 6.5" W x 14" H x 7" HCO
HANGING WEIGHT	: 3.88 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,920 Rated (470 Del.)
BULB	: 2 x 12W LED PCB Integrated , 24W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Indirect

FINISHES OPTION

Black / Gold (BKGLD)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA
DARKSKY

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 35000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com