

BRIGHT STAR

RAZOR

ITEM# 60160 | 3AA Cell LED Flashlight

UPC# 016731601607



Runs Longer, Shines Brighter & This Class I, Div 1 Flashlight Is Now Hands-free!

Features

- One light, 2 modes – High and Low
- Waterproof to one meter
- Drop rating of 2 meters
- Tail cap slot for lanyard

**Large Button
For Gloved Hands**

Clip Magnet



Tail Cap Magnet

**Peak Of 325
Lumens**

Safety Ratings

UL 913
Class I Div 1 & 2 A-D
Class II Div 1 & 2 E-G
Class III Div 1 & 2 T2
ATEX/IECEX/UKCA
II 1G Ex ia op is IIC T2 Ga
Approved for use only with:
KBS Power Solutions MaxX KA2600,
KBS Power Solutions Prime KA2500 ,
Energizer E91 and Rayovac High Energy
LR6

Specifications

Power Source: 3 AA KBS Power Solutions Prime Alkaline Cells (Not Included)

Light Source: Advanced LED Technology

Light Output: 325lm (high) / 125lm (low)

Peak Beam Intensity: 14,000cd (high) / 7,000cd (low)

Beam Distance: 236m (high) / 167m (low)

Run Time: 7 Hours(high) / 24 Hours(low)

Ingress Protection: Waterproof 1 Meter IPX7

Weight: 8oz

Length: 7.125in. **Width:** 2in. **Height:** 2in.

Color: High-Vis Yellow

High Mode		Low Mode	
FL 1 STANDARD		FL 1 STANDARD	