



G-Tek® PosiGrip MAX™

Seamless Knit PolyKor® Blended Glove with PosiGrip MAX™ Coating on Palm & Fingers - Touchscreen

- Seamless construction offers increased comfort and breathability
- Premium PolyKor® blended 18G shell is lightweight and provides excellent dexterity, tactile sensitivity, and cut resistance
- Proprietary PosiGrip MAX™ is a bi-polymer coating that has the best properties of both nitrile and polyurethane
- This unique coating reduces required gripping force by up to 35% in dry/ oily conditions and provides enhanced tactility for handling small parts
- PosiGrip MAX™ coating boasts near 0% oil penetration for safer skin and a reduced rate of glove changeouts from oil exposure
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves
- ⚠ **WARNING:** Cancer - www.P65Warnings.ca.gov



Technical Data

Color	Black
Sizes Available	XS-3XL
Packaging	Bulk Pack
Packed	6 Dozen/Case
Case Dimensions (in)	13.78 x 10.24 x 7.09
Case Weight (lbs)	5.95
Country of Origin	China
Liner Material	PolyKor
Coating	PosiGrip Max
Coating Color	Black
Coating Coverage	Palm & Fingers
Grip	Flat
Gauge	18
Cuff	Knit Wrist
Construction	Coated Seamless Knit, Touchscreen Compatible, Reinforced Thumb Crotch
Certifications	Latex Free

Performance Data

Cut Level	A6
ANSI Abrasion Level	3
ANSI Puncture Level	3
EN 388	4X42F
EN 407	X1XXXX

Care Instructions



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
16-868/XS	Black	XS	198987001124	10198987001121	20198987001128
16-868/S	Black	S	198987001162	10198987001169	20198987001166
16-868/M	Black	M	198987001209	10198987001206	20198987001203
16-868/L	Black	L	198987001247	10198987001244	20198987001241
16-868/XL	Black	XL	198987001285	10198987001282	20198987001289
16-868/XXL	Black	2XL	198987001322	10198987001329	20198987001326
16-868/XXXL	Black	3XL	198987001360	10198987001367	20198987001364