SATCO | NUVO

Project / Job Name:

Location:

Fixture Type:

Notes:



62-3239 - Lyra; 48-Inch LED Vanity; 36 Watt; 3000K-1800K CCT; Dark Bronze Finish; Fluted Glass

DAMP LOCATION · DIMMABLE · ETL · FC · RoHS · CCT SELECTABLE · 30,000 HOURS · 3 YEAR WARRANTY · 120 VOLT · IP 20

GENERAL

Company	NUVO
EA Height	4.75
EA Width	8.25
EA Length	49.25
Mounting Height	4.5
Mounting Length	48.0
Mounting Width	3.38
Bulb Included	Integrated
Glass Finish	Frost
Extends (in)	3.38
Shade Finish	Frost White
Material	Steel / Glass
Includes	Screws and Anchors
Status	Active
Style	Modern and Contemporary
Surge Protection	Built-in surge protection - 1.5KV
Total Harmonic Distortion	<45%
Top To Outlet	2.13
Up Down Installation	Universal
CCT Selectable	Yes
Wattage Selectable	No
Collection	Lyra
Finish Family	Bronze
Amps	0.340A
Lens Finish	Frosted
Lens Material	Glass
Nominal Length	48.0
Power Factor	>0.9
Shade Material	Glass
Shade Shape	Fluted
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	48W
Incandescent Equivalent	195W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K-1800K
Dimmable	Yes-Dimmable
Hours Rated	30000
Beam Angle (degree)	120
Color Temp	Soft White to Warm White
CRI	95+
Dimming Type	Phase Cut (TRIAC)
Operating Frequency	60Hz
Operating Temp	-40F to +194F (-40C to +90C)
Lumens	2800L
Volts	120v
Watts	36W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Dark Bronze
Housing Color	Dark Bronze
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Rectangle

ADDITIONAL INFO

Warranty	3-Years
Rated For Enclosed Fixture	No

PACKAGING

UPC	045923416903
Case Cube	1.1169
Case Height	4.75
Case Length	49.25
Case Quantity	1
Case UPC	10045923416900
Case Weight	14.85
Case Width	8.25
EA Cube	1.1169
EA Height	4.75
EA Length	49.25
EA Quantity	1
EA Weight	14.85
EA Width	8.25
Pack Type	Kraft Box
Web Height	4.5
Web Width	48.0

COMPLIANCE

ADA Compliant	Yes
Air Tight	No
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
IP Rating	IP20
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026