

KEAGAN

PTL3124-PBR/CSE

Keagan is defined by quiet texture and a soft, sculptural form. The ceramic base features a Stria Wheat glaze across a rounded silhouette. Paired with an off-white linen shade, this lamp exudes a tonal simplicity that feels both modern and timeless. Patina Brass hardware at the neck completes the design with understated warmth.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

PATINA BRASS w/ Ceramic Stria Wheat
Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 24"
Width/Diameter: 16.75"
Canopy/Backplate: 4.75"
Product Weight: 14lb
Canopy/Backplate Shape: Oval
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: No

Shade

Shade 1: Textile
Shade 1 Finish: Off White Linen
Shade 1 Top Width: 16.25"
Shade 1 Bottom L/W: 0" / 16.75"
Shade 1 Height: 11"

ELECTRICAL



Bulb 1

Bulb Included: No
Socket: E26 Medium Base
Bulb Type: A19
Max Wattage: 15
Bulb Quantity: 1
Wire Length: 96"
Cord Type: SPT-2 BLACK FABRIC
Switch Type: ON/OFF SWITCH ON SOCKET
Gem Box Required (2"x3"): No
Dark Sky: No

SHIPPING

Carton 1: 19" x 19" x 28"
Carton 1 Weight: 23lb
Shipping Method: Ground
Country of Origin: VN

