

AUTO
BODY SHOP™

PREMIUM



Unleash precision with AmTape® AUTO BODY SHOP™ Masking Tape. This high-performance super Washi paper tape is engineered to meet the demands of the premium automotive refinish industry. Experience exceptional adhesion and residue-free removal across multiple surfaces, from delicate finishes to complex curves. Perfect for bodywork, repairs, auto detailing, IR lamp use, and spray booth applications. Achieve perfect results—every time.



Surfaces

Metal, Rubber, Glass, Plastic.

1 Uses

- Water and solvent-based resistance.
- High-temperature applications.
- Bodywork and repairs.
- Auto-detailing, IR lamps and spray booth.
- Excellent performance on curves profiles.

3 Technical Data

Backing		Super Washi paper
Adhesive		Acrylic Adhesive
UV Resistance		30 days
Physical properties	Standard	Metric
180° peel force	9.12 - 14.59 oz/in	2.5 - 4 N/25mm
Tensile strength	19.99 - 25.69 lbs/in	35-45 N/10mm
Temperature 30min	302°F	150 °C

5 Size

Width	Length
0.70" (18mm)	60 yd (54.8m)
0.94"(24mm)	60 yd (54.8m)
1.41" (36 mm)	60 yd (54.8m)
1.88"(48 mm)	60 yd (54.8m)

2 Features

- Super Washi paper technology designed for superior softness, exceptional flexibility, and no paint bleeding.
- Advanced adhesive technology that enables overlapping and offers solvent resistance.
- Easily removable — up to 90 days indoors and 30 days outdoors — without leaving adhesive residue.
- High-temperature resistant: 150 °C / 302 °F for 30 minutes.
- Sharp edge lines with excellent color separation.
- Can be crumpled and reattached.
- Sticks to masking film and paper.
- Water-repellent.

4 Storage Conditions

- Store in a cool, dry place away from direct sunlight and excessive humidity to maintain film performance. For best results, use this product within one year from the date of production.

6 How to use

- ⌚ Ensure the surface is clean, dry, and dust-free before application.
- ⌚ Apply the tape with firm, even pressure for optimal adhesion.
- ⌚ Remove within 30 minutes if exposed to high temperatures (302°F/150°C).
- ⌚ For best results, peel off slowly at a 45-degree angle to avoid surface damage.

7 Logistic Information

SKU	Size / Description	Cases/pallet	Roll/Case
ABS001-18060PK1	0.70"(18mm) x 60yd (54.8m) AUTO BODY SHOP™ Masking Tape OUTDOOR 60-Day UV-Protected - individually packaged	144	32
ABS001-24060PK1	0.94"(24mm) x 60yd (54.8m) AUTO BODY SHOP™ Masking Tape OUTDOOR 60-Day UV-Protected - individually packaged	144	24
ABS001-36060PK1	1.41"(36mm) x 60yd (54.8m) AUTO BODY SHOP™ Masking Tape OUTDOOR 60-Day UV-Protected - individually packaged	144	16
ABS001-48060PK1	1.88"(48mm) x 60yd (54.8m) AUTO BODY SHOP™ Masking Tape OUTDOOR 60-Day UV-Protected - individually packaged	112	12

WE STICK STRONG