Delphi | E25179-SSN

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Long spans of fluted concrete panels blend Western classicism with modern technology. Scalloped concrete is finished in a Chalky White finish and suitable for damp locations. Choose from stem hung pendants or backlit wall panels that provide ambient lighting and bring tranquility to spaces.



MEASUREMENTS

DIMENSION	: 9.5" L x 9.5" W x 13.75" H
HANGING WEIGHT	: 17.6 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 900 Rated (800 Del.)
BULB	: 1 x 10W LED DC Integrated , 10W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

Sandstone (SSN)

MATERIAL

Concrete, Steel, PC

RATINGS

cETLus
Dry Location

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com