



BURNDY Catalog Number
UPC Number

Description

Status

Web Use

BURNDY Product Line

YA39A5
7818107620288
ALHYLUG 750KCMIL 2HOLE
1/2STUD
Active

Dimensional

Tongue Angle
Strip Length
Length (in)
Tongue Type
Bolt Hole Size (in)
Thickness
B Length (in)
Pad Width (in)
E - in

Straight
2 7/8
7.07
Standard
0.52
0.43
2.46
1.62
1.75

General

Number of Holes

Product Description

2
Aluminum Compression Lug, 2
Hole w/o Inspection Window, 750
kcmil, 1/2" Stud, 1-3/4" Stud Hole
Spacing, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range)
Copper Solid Size (Range)
Copper Stranded (Range)

700 kcmil-750 kcmil
N/A
700 kcmil-750 kcmil

Physical

Type of Plating
Bolt Hole Size
Color Code
Plated (Yes or No)
Index Number
Product Material

Tin - Electro Plated
1/2
Yellow
Y
936
Aluminum

Approvals / Certifications

UL Listed
CSA Certified
ROHS Compatible
UL Recognized
CULUS
Industry Standards

Y
Y
Compliant
N
N
UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175