Tree Hugger | E42313-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

LED spot light modules are connected with rotating joints designed to strap along vegetation and posts. Available in groupings of three, five, and eight, each section is supplied with a fabric strap to easily wrap the products around various structures. These are low voltage rated for inputs of 12-24V and require a landscape transformer that is not provided.



MEASUREMENTS

DIMENSION	: 11.5" W x 3" H
HANGING WEIGHT	: 1.98 lb

LAMPING

INPUT VOLTAGE	: 12V
LUMENS	: 1,500 Rated (1,030 Del.)
BULB	: 3 x 5W LED AC/DC Integrated , 15W Total
BULB INCLUDED	: (Included)
DIMMABLE	: N
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum, Glass,Plastic

RATINGS

cETLus
Wet Location

ADDITIONAL

RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com