



NOVAX®

Class 4 Rubber Insulating Glove with Bell Cuff - 16"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Bell cuff increases comfort on the job
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date
- Meet ANSI/ASTM D120 standard

Technical Data

Color	Black
Sizes Available	8.5-12
Packaging	Boxed
Packed	6 Pair/Case
Case Dimensions (in)	16.93 x 17.13 x 20.00
Case Weight (lbs)	17.77
Country of Origin	Malaysia
Certifications	ASTM D120

Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
161-4-16/8.5	Black	8.5	616314692765	10616314692762	20616314692769
161-4-16/9	Black	9	616314692772	10616314692779	20616314692776
161-4-16/9.5	Black	9.5	616314692789	10616314692786	20616314692783
161-4-16/10	Black	10	616314692796	10616314692793	20616314692790
161-4-16/10.5	Black	10.5	616314692802	10616314692809	20616314692806
161-4-16/11	Black	11	616314692819	10616314692816	20616314692813
161-4-16/11.5	Black	11.5	616314692826	10616314692823	20616314692820
161-4-16/12	Black	12	616314819582	10616314819589	20616314819586