SATCO | NUVO



Project / Job Name:

Location:

Fixture Type:

Notes:

S30111 - LED Multi-Light; 4000 Max Lumens; USB-C Rechargeable; 3.7 Volt; 12pc Tray Pack

DIMMABLE | FC | RoHS COMPLIANT | 1 YEAR WARRANTY

GENERAL

Company	SATCO
EA Height	7.25
EA Width	3.25
EA Length	2.0
Material	Aluminum
Fixture Type	Rechargeable Search
Includes	USB-A to USB-C Charging Cable
Product Notes	Integrated Rechargeable 3.7V ion Battery; Power Bank: 2600mAh; Charge Time: 4HRS
Status	Active
CCT Selectable	No
Wattage Selectable	No
Finish Family	Black
Additional Info	Ships in retail-ready display trays and packaging
Integrated Features	Power Bank; Beam Adjustable; Telescopic Lantern; Digital Display; Magnetic Base; Turbo
Lens Finish	Frost
Lens Material	Acrylic
Lensed	Yes
Portable Light Modes	High, Low, Medium, Turbo
Product Technology	LED
Serviceable Battery	No
Beam Distance (Ft)	1312
Battery Indicator	Yes
Digital Display	Yes
Drop Impact Rating	3.28 Ft (1M)
Battery Operating Temp	+32F to +104F (0C to +40C)
Light Source Quantity	Double
Power Bank Storage	2600mAh

ELECTRICAL

CCT (Kelvin Temp)	6500K
Dimmable	Yes-Dimmable
Color Temp	Daylight
CRI	50+
Dimming Type	Only dimmable via setting selection, Step Dimming
Operating Temp	+32F to +104F (0C to +40C)
Lumens	4000L/2000L/1000L/400L/150L/50L
Volts	3.7V
Max Lumens	4000L
Connection	USB-C Rechargeable
Charge Time	4hr
Battery Chemistry	Lithium-ion (Li-ion)
Replaceable Battery Type	18650
USB Type In	1 USB-C
USB Output Charging Power	(1) 1A 5V
USB Type Out	1 USB-A 1A

PHYSICAL

Finish	Black / Gray / Red
Housing Color	BlackGrayRed
Mounting Procedure	Magnetic Base

ADDITIONAL INFO

Warranty	1-Year
Installation Notes	Do Not Charge The Product Below 40F Or above 104F; Do Not Exceed 5V DC, 1A Charging
Portable Light Functions	LED Lantern Function, Red Light Function, White Light Function

PACKAGING

UPC	045923300127
Case Cube	1.3177
Case Height	10.23
Case Length	11.42
Case Quantity	24
Case UPC	10045923300124
Case Weight	23.67
Case Width	19.49
EA Cube	0.0273
EA Height	7.25
EA Length	2.0
EA Quantity	1
EA Weight	0.8
EA Width	3.25
Inner Cube	0.4264
Inner Height	8.43
Inner Length	8.74
Inner Quantity	12
Inner UPC	20045923300121
Inner Weight	11.3
Inner Width	10.0
Pack Type	Color Box
Web Height	6.8
Web Length	1.81
Web Width	1.81

COMPLIANCE

CA Prop 65	Lead
FCC Compliant	Yes
IP Rating	IPX4
ROHS Compliant	Yes
Energy Star Certified	No
T24/JA8 Compliant	No
Performance Standards	ANSI PLATO FL1

© Satco Products, Inc.
All rights reserved 2026