



Post Office Box 97  
 Benton Harbor, Michigan  
 Ph: 269/926-6171  
 Fax: 269/925-8288

PART NUMBER:

STD114

REVISION:

K

Model Number	MAX. PRESS.		MAX. SPEED	HP	kW	Net Wt.	
	bar.	PSI				lbs.	kg
2AM-FCC-1	7.0	100	3,000 RPM	.95	0.70	4.4	2.0
2AM-FCC-1B	7.0	100	3,000 RPM	.95	0.70	4.4	2.0
2AM-FCW-13	7.0	100	3,000 RPM	.95	0.70	4.4	2.0
* 2AM-FCW-13B	7.0	100	3,000 RPM	.95	0.70	4.4	2.0

SOUND LEVEL 76 dB(A) MAX.

NORMAL AMBIENT +1°C. - 120°C.

RELATIVE HUMIDITY 0% - 100%

ENVIRONMENT HAZARDOUS AMBIENT COMBUSTIBLE  
GAS AND DUST +1±C TO +40±C

CONFORMS TO EUROPEAN STD. EN13463-1 NON-ELECTRICAL  
 EQUIPMENT FOR EXPLOSIVE ATMOSPHERES GROUP II, CAT. 2  
 (GAS & DUST) PROTECTED BY CONSTRUCTION  
 (SURFACE TEMP. RATING 135±C)

NOTES:

- 1) TECHNICAL DATA SUBJECT TO CHANGE WITHOUT NOTICE.
- 2) ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.
- 3) \* DENOTES INACTIVE.

