



QRP® PolyTuff®

Cold Handling Polyurethane Glove with Thermal Cotton Lining - 11"

- Extreme cold weather glove for environments from -30C to -60C range (-22F to -76F)
- Two layer construction
- Polytuff urethane outer shell
- Durable thermal cotton lining
- Exceptional wet/dry grip due to our aggressive, but non-marring, embedded gritty grip

Technical Data

Color	Yellow
Sizes Available	L-2XL
Packaging	Bagged Pair
Packed	1 Pair/Case
Case Dimensions (in)	13.00 x 7.00 x 4.00
Case Weight (lbs)	3.00
Country of Origin	Japan
Polymer	Polyurethane
Grip	Rough
Cuff	Straight
Length	11"
Construction	Supported
Certifications	TAA Compliant

Performance Data

Temperature Resistant	Extreme Cold
-----------------------	--------------

Care Instructions



Machine Wash



Water Temp 40°C



Do Not Bleach



Tumble Dry



Low Heat

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
102L	Yellow	L	616314277658	10616314277655	20616314277652
102XL	Yellow	XL	616314277665	10616314277662	20616314277669
1022X	Yellow	2XL	616314277573	10616314277570	20616314277577