

Schedule 80 CPVC Product
CPVC Schedule 80 Fittings

**Tees**

Part Number	Size	Std Pk	Mstr Ctn	Prod Code
-------------	------	--------	----------	-----------

Part Number	Size	Std Pk	Mstr Ctn	Prod Code
-------------	------	--------	----------	-----------

Tee - Street (continued)**Spigot x Socket x Socket**

844-010C	1	15	0	090
844-012C	1-1/4	10	0	090
844-015C	1-1/2	10	0	090
844-020C	2	10	0	090

Tee - Reducing**Socket x Fipt x Socket**

803-095C	3/4X1/2X3/4	50	0	090
----------	-------------	----	---	-----

90° Ells**Tee - Special Reinforced Reducing****Socket x SR Fipt - Stainless Steel Collar x Socket****90° Ell****Socket x Socket**

(See also Gauge & Instrument Fittings for additional configurations)

803-095CSR	3/4X1/2X3/4	15	0	096
------------	-------------	----	---	-----

Tee**Fipt x Fipt x Fipt**

805-002C	1/4	25	150	090
805-003C	3/8	25	150	090
805-005C	1/2	20	120	090
805-007C	3/4	15	120	090
805-010C	1	15	0	090
805-012C	1-1/4	10	0	090
805-015C	1-1/2	10	0	090
805-020C	2	10	0	090
805-025C	2-1/2	5	0	090
805-030C	3	5	0	090
805-040C	4	5	0	090
805-060CF ¹	6	1	2	090
805-080CF ¹	8	1	0	090

¹ Sized with Female Adapter

806-002C	1/4	50	300	090
806-003C	3/8	25	150	090
806-005C	1/2	20	240	090
806-007C	3/4	20	160	090
806-010C	1	25	0	090
806-012C	1-1/4	10	0	090
806-015C	1-1/2	10	0	090
806-020C	2	25	0	090
806-025C	2-1/2	5	0	090
806-030C	3	6	0	090
806-040C	4	5	0	090
806-050C	5	4	0	090
806-050CF	5	1	4	097
806-060C	6	4	0	090
806-080C	8	2	0	090
806-080CF	8	1	0	097
806-100C	10	1	0	091
806-100CF	10	1	0	097
806-120C	12	1	0	091
806-120CF	12	1	0	097
806-140C	14	1	0	095
806-140CF	14	1	0	097
806-160CF	16	1	0	097
806-180CF	18	1	0	097
806-200CF	20	1	0	097
806-240CF	24	1	0	097

Tee - Special Reinforced**SR Fipt x SR Fipt x SR Fipt - Stainless Steel Collar**

805-002CSR	1/4	25	150	096
805-003CSR	3/8	25	150	096
805-005CSR	1/2	25	150	096
805-007CSR	3/4	25	100	096
805-010CSR	1	15	0	096
805-015CSR	1-1/2	10	0	096
805-020CSR	2	10	0	096

90° Ell - Sweep**Socket x Socket**

806-005SC	1/2	25	150	090
806-007SC	3/4	25	100	090
806-010SC	1	20	0	090
806-012SC	1-1/4	25	0	090
806-015SC	1-1/2	25	0	090
806-020SC	2	25	0	090

Tee - Street**Spigot x Socket x Socket**

844-005C	1/2	25	200	090
844-007C	3/4	15	120	090

Made in the U.S.A.

Suitable for Oil-Free air handling to 25 psi, not for distribution of compressed air or gas
See MSRP-1 Sheet or Check Spears® On-line Catalog @ www.spearsmfg.com for Pricing