



Howard Leight™ Maximum Lite T-Shape Disposable Soft Polyurethane Foam Corded Ear Plugs - NRR 30

- Low pressure polyurethane foam expands gently for comfortable long-term use
- Contoured T-shape design for easy insertion and wear
- Ideal size for workers with smaller ear canals
- Smooth, soil-resistant skin prevents dirt build-up
- Great medium-to-high protection with an NRR of 30dB

Technical Data

Color	Green
Sizes Available	OS
Packaging	Bulk Boxed
Packed	1250 Pair/Case
Case Weight (lbs)	0.00
Country of Origin	United States
Hearing Style	Corded
Ear Plug Material	Polyurethane Foam
Box Count	5
EN 352	EN352-2: Earplugs
Certifications	TAA Compliant

Performance Data

NRR Rating (ANSI S3.19-1974)	30
SNR Rating	34
SLC 80 Class	Class

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
LPF-5-30	Green	OS	1003355202058		