SATCO | NUVO

Project / Job Name:

Location:

Fixture Type:

Notes:



62-8128 - Amalfi; 14-Inch LED Flushmount; 23 Watt; 3000K/4000K/5000K CCT Selectable; Smoked Graphite; Alabaster Stone Lens

DAMP LOCATION | 90+ CRI | DIMMABLE | ETL US | FC | RoHS COMPLIANT | CCT SELECTABLE | 30,000 HOURS | AIR TIGHT | 3 YEAR WARRANTY | 120-277V

GENERAL

Company	NUVO
EA Height	5.7
EA Width	16.5
EA Length	16.5
Mounting Height	0.75
Mounting Length	14.0
Mounting Width	14.0
Bulb Included	Integrated
Diameter	14.0
Material	Steel
Includes	Mounting Strap/Plastic Anchors
Status	Active
Style	Transitional
Surge Protection	Built-in surge protection - 2KV
Total Harmonic Distortion	45%
Top To Outlet	8.0
Up Down Installation	Down
CCT Selectable	Yes
Wattage Selectable	No
Collection	Amalfi
Finish Family	Gray
Amps	0.190A
Lens Finish	Alabaster
Lens Material	Alabaster Stone
Lensed	Yes
Nominal Length	12.5
Power Factor	>0.9
Indoor Outdoor	Indoor
Product Technology	LED
Fluor Equiv	60W
Incandescent Equivalent	200W
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	30000
Beam Angle (degree)	120
Color Temp	Soft White to Daylight
CRI	90+
Dimming Type	Phase cut
Operating Frequency	60Hz
Operating Temp	-14F to +104F (-10C to +40C)
Lumens	2070L
Volts	120V-277V
Watts	23W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Smoked Graphite
Housing Color	Smoked Graphite
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round

ADDITIONAL INFO

Warranty	3-Years

FEATURES

Flicker Free	Yes

PACKAGING

UPC	045923416989
Case Cube	2.1396
Case Height	12.6
Case Length	17.13
Case Quantity	2
Case UPC	10045923416986
Case Weight	22.0
Case Width	17.13
EA Cube	0.898
EA Height	5.7
EA Length	16.5
EA Quantity	1
EA Weight	10.34
EA Width	16.5
Pack Type	Kraft Box
Web Height	3.13
Web Width	14.0

COMPLIANCE

ADA Compliant	No
Air Tight	Yes
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
IC Rated	No
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cETLus
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No

© Satco Products, Inc.
All rights reserved 2026