



EAN:	4013288196651	Size:	122x83x22 mm
Part number:	05078699001	Weight:	158 g
Article number:	7781	Country of origin:	TW
		Customs tariff number:	82079099

- Square head insert tool 14x18 mm
- For torque wrenches from the Click-Torque X series with 14x18 mm mounting
- Application: Hexagon screw heads or nuts
- With safety pin
- The chrome-vanadium steel version makes the plug-in tools suitable for heavy loads

Ring spanner insert, for hexagon screw heads or nuts; for torque wrenches of the Click-Torque X series with 14x18 mm holder.

Web link
<https://www.wera.de/en/05078699001>

Wera - 7781
05078699001 - 4013288196651

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Drive 14x18 mm

Chrome vanadium steel

With pin lock



For torque wrenches from the Click-Torque X series with 14x18 mm mounting.



The insert tools are suitable for high loads thanks to their chrome-vanadium steel design.



Safe working and rapid tool change thanks to the pin lock of the insert tools.

Further versions in this product family:

							
	mm	mm	mm	mm	mm	mm	mm
05078690001	14x18	13	25.5	61.6	36.6	30	11.0
05078691001	14x18	14	25.5	63.0	38.0	30.1	11.0
05078692001	14x18	15	25.5	63.5	38.5	29.8	11.0
05078693001	14x18	16	25.5	65.0	40.0	29.8	12.0
05078694001	14x18	17	25.5	65.0	40.0	29.8	12.0
05078695001	14x18	18	25.5	66.3	41.3	30.6	13
05078696001	14x18	19	25.5	66.1	41.1	30.6	13
05078697001	14x18	21	25.5	67.7	42.7	33.5	15.0
05078698001	14x18	22	25.5	67.5	42.5	34.3	15.0
05078699001	14x18	24	25.5	70.5	45.5	37.5	15.0
05078700001	14x18	27	25.5	73.2	48.2	42.7	17.0
05078701001	14x18	30	25.5	74.1	49.1	46.3	19.0
05078702001	14x18	32	25.5	76.5	51.5	47.3	19.0
05078703001	14x18	34	28.0	81.0	56.0	52.5	19.0
05078704001	14x18	36	28.0	81.8	56.8	53.8	19.0
05078705001	14x18	41	30.0	87.1	62.1	60.7	20.0

Web link
<https://www.wera.de/en/05078699001>

Wera - 7781
 05078699001 - 4013288196651

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de