

GALENA

538-24-VGL

Boldly botanical, the Galena chandelier is characterized by a bowl-shaped silhouette with a central candelabra cluster. Each piastre glass petal is etched with vein-like detailing that adds to the sense of realism. A sculpted metal sepal gathers the petals, coordinating with the Vintage Gold Leaf-finished suspension. Available with 6 or 9 lights.

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 8"

Width/Diameter: 24"

Minimum Height: 13.75"

Maximum Height: 78.75"

Canopy/Backplate: 5.5"

Hanging Type: 72" Chain

Product Weight: 28lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Piastre Inside Optic and Etched

Shade 1 Top Length: 11"

Shade 1 Top Width: 7.75"

Shade 1 Height: 7.5"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 6

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 19" x 16" x 23"

Carton 1 Weight: 42lb

Shipping Method: Ground

Country of Origin: PH

